

# **TECHNICAL DATA SHEET**

01/03/2019	DOC152071

Designation	SITUO io
References	1870311 to 1870314 Situo 1 io Pure II 1870315 to 1870318 Situo 1 io Iron II 1870319 to 1870322 Situo 1 io Natural II 1870323 to 1870326 Situo 1 io Arctic II 1870327 to 1870330 Situo 5 io Pure II 1870331 to 1870334 Situo 5 io Iron II
	1870335 to 1870338 Situo 5 io Natural II 1870339 to 1870342 Situo 5 io Arctic II
Range	SITUO

## **FUNCTIONS**

# Situo 1 & 5 io are designed to manage io applications.

- Up/Turn on/Open (short press), Dim & Tilt UP (long press) function on "Up" button
- **Stop** function on "Stop/My" button
- Down/Turn off/Close (short press), Dim & Tilt down (long press) function on "Down" button
- My button allows to define a favorite position of the application.
- A select button able to select a channel (on the Situo 5 io only)

At each pressing of a button, the transmitter emits radio orders and green led lights on during the time the button is pressed (to confirm order emission)

The programming button located at the back cover of the transmitter allows to memorize the address of the transmitter in one or several receivers. It is the pairing process.

# Situo 1 io II



# Situo 5 io II







Iron

Arctic

TECHNICAL SPECIFICATIONS				
Box	Material Colors Size	TBC (ABS) Pure / Arctic / Natural / Iron 149 x 42 x 16 mm		
Weight (remote + battery only)	Gramme	46g		
Battery	Voltage Type Lifetime (at ambient temperature)	3V CR 2032 5 years (4 orders per day/per channel)		
Radio frequency	MHz	For Europe and all countries applying and allowing io technology: 868 MHz		
Radio power	Min dBm	+3 dBm		
Radio range	Free field	For 1 channel remote control: Min 50m in free field Use guaranteed in most « Room installation » depending on the environment.		
		For 5 channels remote control: Min 150m in free field Use guaranteed in « Floor installation » depending on the environment		
Modulation type Protocol Antenna		FSK io homecontrol Integral		
Temperature range	Storing Working	- 20°C / +60°C 0°C / +48°C		
Standards	Electromagnetic compatibility	EN 61000-4-2 EN 61000-4-3 EN 301489-1 EN 301489-3		
	Electrical safety	EN 62368-1		
	Protection on the health	EN 62479		
	Radio	EN 300220-2		

#### **DESCRIPTION**



#### **COMPATIBILITIES**

See compatibility matrix

#### **USAGE**

Press on "**Up**" button sends open / switch on the applications (Roller shutters, Screens, Awnings, Lights, EVBs ...)

Press on "**Down**" button sends close / switch off the applications (Roller shutters, Screens, Awnings, Lights, EVBs ...)

Short press on "My" sends **stop** if actuator is moving.

Short press on "My" sends actuator to **favourite predetermined position** order if actuator is already stopped.

On the Situo 5 Variation io, use **channel button** to choose the channel you want to control.

The channel(s) LED indicate which channel is currently selected

Note that some specific ergonomics could be applied (see actuators leaflets for further information).

## **INSTALLATION**

## My setting

Long press (5secs) on "My" saves "My" position inside the actuator.

If the actuator is already in "My" position, it will erase the "My" position. (depending on the actuators)

# **Prog (pairing process)**

Short press (0,5secs) on Prog to pair your product to a "waked up" actuator.

Long press (2secs) on Prog to wake up the actuator already paired.

## Rolling code

The first code is automatically set in factory.

At each control given by the transmitter, the code is automatically changed (rolling code, 16 million of possibilities).

SOMFY Actuators settings and re-settings with multiple press of Up, My and Down buttons (see actuators leaflets).